Sumitomo Drive Technologies

<image>

RIGHT ANGLE GEARBOXES, DEDICATED FOR COOLING TECHNOLOGY

Hansen M5CT

Overview

- Vertical Right Angle 2-stage industrial gearbox series.
- Specifically designed for Cooling Technology applications:
 - Wet Cooling Tower fan drives
 - Air Cooled Condenser fan drives.
- Dedicated product: cost efficient, robust & easy to maintain.
- Available in 7 sizes (13-53 kNm).



Advantages of Hansen M5CT Cooling Technology series

- Dedicated industrial gearbox
 Best possible fit for Wet Cooling Towers and Air Cooled
 Condensers (induced draft types)
- Designed in accordance with CTI standards
 Manufactured to be compliant with Cooling Technology Institute (CTI) specifications
- Best out of Hansen P4, Hansen M4ACC and PARAMAX SFC Rely on decades of experience and more than 20.000 installations in the field
- Rigid housing, dynamic stability
 Smooth transition of high axial loads coming from the rough application
- Optimized gearing from Hansen P4 range
 Proven design, maximum load capacity, minimum losses and quiet operation

- Advanced design to withstand the peak fluctuations during start-up Selection method taking starts and stops into account, specifically for ACC applications
- Reliable lubrication and sealing, less maintenance Oil lubrication without outsides pipes, Oil seal hood for reliable protection against the ingress of dust & water
- High resistance in corrosive and extreme humidity environments Standard high-quality paint conform ISO C5 corrosion category, stainless steel bolts, use of durable instruments
- Numerous instruments & accessories

E.g. Optional condition monitoring: Temperature, oil flow and vibrations



Technical Information

13 - 53 kNm Output Torque	7 sizes Dedicated			tages it-angle	6.3 - 22.4 Reduction Ratios			
Size Range	CA	DA	DX	EA	EX	FA	FX	
Nominal Output Torque	13 kNm	18 kNm	23 kNm	28 kNm	36 kNm	41 kNm	53 kNm	
Output shaft Direction	Vertical up	Vertical upward						
Shaft type	Solid shaft	Solid shaft						
Shaft configuration Right Angle								
Gears	Helical and	Helical and Bevel gears - designed and rated in accordance with AGMA						
Housing Type	Dedicated l	Dedicated housing with integrated cooling fins						
Lubrication Type	Standard o	Standard oil splash and optional pump, both without outside piping						
Bearings output shaft	Extended B	Extended Bearing span with heavy-duty roller bearings						
Input speed	Up to 1800	Up to 1800 rpm						

Hansen Industrial Transmissions NV | Leonardo da Vincilaan 1-3 | 2650 Edegem | Belgium Tel. +32 3450 1211 | E-Mail: HIT.info@shi-g.com | www.sumitomodrive.com

Sumitomo (SHI) Cyclo Drive Germany GmbH | Cyclostraße 92 | 85229 Markt Indersdorf | Germany Tel. +49 8136 66-0 | E-Mail: SCG.info@shi-g.com | www.sumitomodrive.com